

Important things about the new 40X silicone immersion objective



(This 40X Silicone lens replaced with the damaged 40X oil one on 5 Sept 2018)



1. Technical info

Objective	W.D. mm	Magnification	FN	NA	Immersion	Chromatical correction	Correction collar
UPLSAPO 40X S	0.3	40X	22	1.25	Silicone oil	Yes. 3 colors	Yes

2. **Features:** brighter and therefore more sensitive compared to oil and water objectives

3. Selecting the 40X Silicone lens

From software 
or from hardware 



4. Important notes:

- Only use silicone oil (green bottle)!
- Use of correction collar. 0.17 for 1.5# coverslip at 23°C.

